


# piGRIP™

Taking gripping to new dimensions



# piGRIP™ Versatility and productivity

A modular suction cup that fits most machines and that can be optimized for handling almost all materials. piGRIP™'s five different lip types ensure the right hardness/softness and sealing capability for your material. Combined with the firm bellows, piGRIP™ is stable enough to handle faster accelerations and more high speed lifts as compared to traditional cups.



*With traditional single durometer cups, where the lips and bellows are made of the same material, you either have to compromise on the grip or the machine handling speed. That is now history with piGRIP™, the efficient automation innovation from Piab.*

- ▶ Materials that are in accordance with **FDA** are available for the food industry.
- ▶ **100% Recyclable** and separable material contribute to an environmental friendly and sustainable waste management program as opposed to cup materials like PVC.
- ▶ Can be used in **high temperature** applications such as injection molding. Material options free from silicone and Paint Wetting Impairment Substances (PWIS).



Product Group
piGRIP™
Code
G

Lip			
Dimension & Type		Material & Durometer	
Code	Description	Code	Description
S25	Ø 25 mm Standard lip	T60 T50	TPE 60° Shore A TPE 50° Shore A
S35	Ø 35 mm Standard lip		
S50	Ø 50 mm Standard lip		
S70	Ø 70 mm Standard lip		
FX28	Ø 28 mm Flexible lip	T50 T30	TPE 50° Shore A TPE 30° Shore A
FX39	Ø 39 mm Flexible lip		
FX55	Ø 55 mm Flexible lip		
FX77	Ø 77 mm Flexible lip		
FLI25	Ø 25 mm Foam lip	S	Foam EDPM (soft)
FLI35	Ø 35 mm Foam lip		
FLI50	Ø 50 mm Foam lip		
FLI70	Ø 70 mm Foam lip		

Lips are available as spare parts.

Bellows or Flat Cup	
Code	Description
B1	1 bellows
B3	3 bellows
F	Flat

Support	
Code	Description
S1	Support type 1



**G . S50T60 . B3 . S1 . G38M . 01 ( . )**



**Fitting**

Type		Size		Style	
Code	Description	Code	Description	Code	Description
G NT	G-Thread NPT-Thread	18	1/8"	M	Male
		14	1/4"		
		38	3/8"		
		12	1/2"		
GL NTL	G-Thread low NPT-Thread low	18	1/8"	M	Male
		14	1/4"		
		38	3/8"		
NS G*	NPSF-Thread G-Thread	18*	1/8"	F	Female
		14	1/4"		
		38	3/8"		
		12	1/2"		
		518*	5x1/8"		
NT	NPT-Thread	14	1/4"	F	Female
		38	3/8"		
M	M-Thread	M6	M6	M	Male
		MF8	M8x1		
		M10	M10		
		MF14	M14x1		
		MF16	M16x1.5		
M	M-Thread	M5	M5	F	Female
		M6	M6		
		M8	M8		
		M10	M10		
		M12	M12		
		MF16	M16x1.5		
U	UNC-Thread	12	1/2"	F	Female
X	No Type	X	No Size	X	No style

\*) Fitting code G18F and G518F are automatically changed to NS18F and NS518F due to identical threads. Fittings are available as spare parts.



**Option**

Code	Description
00	No Filter
01	Filter mesh
02	Filter disc (only bellows cup)



**FDA approved option includes material certificate**

Code	Description
FDA	US Food and Drug Administration

\*) Leave blank for no certificate. Certificate includes a fee.

## Thousands of suction cups ready to improve your machine

A unique modular suction cup concept with individually optimized parts for gripping, lifting and height compensation.



A large selection of **fittings** makes piGRIP™ cups ready to fit new machines and easy to retrofit existing cups.

One **support** per size works as a gateway for all bellows and lips (flat cups).

Firm and Stable 1- and 3- folded **bellows** allows for faster machine speeds. Thin-wall design makes them faster to compress using less force and energy. The strength of the material increases lifting capacity between 30-50% compared to similar conventional cups.

A low micron **filter disc** inside the bellows traps dust and particles increasing system reliability.

Get an excellent grip on almost anything with the right **lip** for your application. Choose standard lips from 60° shore to extremely flexible, soft lips in 30° shore. Even foam lips for objects which are difficult to grip with traditional cups.



80°-87°	TPE, Oil resistant, Silicone/PWIS free & Mark free
80°-87°	TPE, FDA, Oil resistant, Silicone/PWIS free & Mark free
60°	TPE, Oil resistant, Silicone/PWIS free & Mark free
50°	TPE, FDA
30°	TPE, FDA
60°	PU
S	EPDM, Foam

# piGRIP™

Superior performance with individually optimized parts.



## Standard lip (S)

– for versatile use

- ▶ The green standard lip is suitable for relatively even surfaces on sealed materials. It has extra wear resistance.
- ▶ The blue standard lip is recommended if the surface is more uneven or rough, e.g. textured plastic parts. FDA approved material recommended for food handling.



## Flexible lip (FX)

– with extra sealing capability


- ▶ The flexible lips are suitable for surface leaking materials (wrinkled or textured) and porous materials, such as corrugated paper.
- ▶ Both the blue and yellow lips have FDA approved material and are recommended for food handling.



## Foam lip (FLI)

– for difficult to handle objects

- ▶ Suitable when conventional lips are not sealing enough.
- ▶ Can replace mechanical grippers.
- ▶ A lip holder excludes the need for glue, worn lips are easy replaced.





## Support – the generic interface

- ▶ Gateway between fittings and bellows or lips (for flat cups).
- ▶ Adds cleats with good wear resistance and friction to flat cups.




## Bellows – when level compensation is needed

- ▶ Firm/stable bellows allows for high machine speeds.
- ▶ Low spring force with thin-wall design, makes it easy to compress and return, leading to faster evacuations and speeds.
- ▶ Extra high lifting force compared to conventional cups in the same size. The stiff bellows retains its shape even at deep vacuum levels.




## Fitting - huge selection for many machines and industries

- ▶ All fittings are possible to use for all configurations. Easy to upgrade/change.



Suction cup dimensions, in

Lip type & size	Dim. A	Dim. B.			
		F (Flat)	B-1 (1 Bellows)	B-3 (3 Bellows)	
	S25	0.98	0.43	0.74	1.17
	S35	1.38	0.49	0.92	1.53
	S50	1.97	0.58	1.19	2.06
	S70	2.76	0.70	1.56	2.78
	FX28	1.10	0.45	0.76	1.19
	FX39	1.54	0.52	0.94	1.56
	FX55	2.17	0.62	1.23	2.10
	FX77	3.03	0.76	1.61	2.83
	FLI25	0.98	1.04	1.35	1.79
	FLI35	1.38	1.09	1.52	2.13
	FLI50	1.97	1.15	1.76	2.63
	FLI70	2.76	1.23	2.09	3.31



Build height:


$$H = B + C = 0.74 + 0.20 = 0.94 \text{ in.}$$

Fitting dimensions, in

Type	Code	Dim. C	Dim. D	Description	Recommended fitting size for best performance*			
					S25 FX28 FLI25	S35 FX39 FLI35	S50 FX55 FLI50	S70 FX77 FLI70
	G18M	0.20	0.24	Fitting G1/8" male	x	x	x	
	G14M	0.24	0.35	Fitting G1/4" male	x	x	x	x
	G38M	0.24	0.39	Fitting G3/8" male		x	x	x
	G12M	0.24	0.39	Fitting G1/2" male			x	x
	GL18M	0.06	0.24	Fitting G1/8" low male	x	x	x	
	GL14M	0.06	0.35	Fitting G1/4" low male	x	x	x	x
	GL38M	0.06	0.39	Fitting G3/8" low male		x	x	x
	NT18M	0.20	0.28	Fitting 1/8" NPT male	x	x	x	
	NT14M	0.24	0.43	Fitting 1/4" NPT male	x	x	x	x
	NT38M	0.24	0.45	Fitting 3/8" NPT male		x	x	x
	NT12M	0.24	0.59	Fitting 1/2" NPT male			x	x
	NTL18M	0.06	0.28	Fitting 1/8" NPT low male	x	x	x	
	NTL14M	0.06	0.43	Fitting 1/4" NPT low male	x	x	x	x
	NTL38M	0.06	0.45	Fitting 3/8" NPT low male		x	x	x
	MM6M	0.20	0.24	Fitting M6 male	x	x		
	MMF8M	0.20	0.24	Fitting M8 x 1 male	x	x	x	
	MM10M	0.24	0.39	Fitting M10 male	x	x	x	
	MMF14M	0.24	0.47	Fitting M14 x 1 male	x	x	x	x
	MMF16M	0.24	0.47	Fitting M16 x 1.5 male		x	x	x
	G14F	0.39	-	Fitting G1/4" fem	x	x	x	
	G38F	0.51	-	Fitting G3/8" fem		x	x	x
	G12F	0.55	-	Fitting G1/2" fem			x	x
	NS18F	0.28	-	Fitting 1/8" NPSF fem	x	x	x	
	NS14F	0.39	-	Fitting 1/4" NPSF fem	x	x	x	x
	NS38F	0.51	-	Fitting 3/8" NPSF fem		x	x	x
	NS12F	0.55	-	Fitting 1/2" NPSF fem			x	x
	NS518F	0.71	-	Fitting 5x1/8" NPSF fem	x	x	x	
	NT14F	0.47	-	Fitting 1/4" NPT fem	x	x	x	x
	NT38F	0.51	-	Fitting 3/8" NPT fem		x	x	x
	U12F	0.47	-	Fitting 1/2" UNC fem			x	x
	MM5F	0.24	-	Fitting M5 fem	x	x		
	MM6F	0.24	-	Fitting M6 fem	x	x		
	MM8F	0.28	-	Fitting M8 fem	x	x	x	
	MM10F	0.28	-	Fitting M10 fem	x	x	x	
	MM12F	0.47	-	Fitting M12 fem	x	x	x	
	MMF16F	0.51	-	Fitting M16 x 1.5 fem		x	x	x

\*) No flow restriction or excessive volume to evacuate, which will deteriorate the performance of the vacuum system.  
 \*\*) Fitting code G18F and G318F are automatically changed to NS18F and NS518F due to identical threads.

Up to 50% improved lifting force with piGRIP™. Use fewer cups or smaller sizes.



Proven function and lifting capacity within specified area of operation.  
See suction cup selection guide on [www.piab.com](http://www.piab.com) for specified performance data.

Material Specifications

Material	Hardness Shore A °	Item(s)	Color	Temp. range ° F	Special qualities
TPE	80-87	Support S1	Lime/Transparent	-4-176/248*	FDA**, Silicone/PWIS free, Mark free, oil resistant
TPE	87	Bellows	Lime/Transparent	-4-176/248*	FDA**, Silicone/PWIS free, Mark free, oil resistant
TPE	60	Standard Lip (S) T60	Green	-4-176/248*	Silicone/PWIS free, Mark free, oil resistant
TPE	50	Standard Lip (S) T50	Blue	-40-176/248*	FDA
TPE	50	Flexible Lip (FX) T50	Blue	-40-176/248*	FDA
TPE	30	Flexible Lip (FX) T30	Yellow	-40-176/248*	FDA
EPDM	-	Foam Lip (FLI)	Black	-40-248*	Ultra soft cellular rubber
PU	60	Foam Lip holder	Green	50 – 122	

\*)Max. Temperature short term contact, <10 seconds and 50% intermittance, ambient temperature 59-86 °F, mechanical properties will start to degrade.  
\*\*) FDA approved option in transparent material.

Go to suction cup selection guide on  
[www.piab.com](http://www.piab.com)  
to configure your suction cup.

## AMERICAS

### ARGENTINA

Piab Argentina S.A.  
25 de Mayo 1807  
San Martín  
AR-1650 BUENOS AIRES  
Phone: +54 11 4713 8550  
Fax: +54 11 4713 8552  
Email: info-argentina@piab.com

### BRAZIL

Regional office South America  
Piab do Brasil Ltda.  
R. Capitão Joaquim da Silva Rocha, 50  
Jardim Ana Maria  
BR-13208-750 JUNDIAI – SP  
Phone: +55 11 4492 9050  
Fax: +55 11 4522 4066  
Email: info-brasil@piab.com

### MEXICO

Piab Mexico & Central América  
Querétaro, Mexico CP. 76190  
Phone: +52 (442)228-5894  
Email: info-mxca@piab.com

### USA/CANADA

Regional office North America  
Piab USA, Inc.  
65 Sharp Street  
HINGHAM MA US-02043  
Phone: +1 781 337 7309  
Fax: +1 781 337 6864  
Email: info-usa@piab.com

## ASIA

### CHINA

Piab (Shanghai) Co., Ltd  
Unit 401, Blk B1, No. 6000 Shenzhuan Rd  
Songjiang District  
CN-201619 SHANGHAI  
Phone: +86 21 5237 6545  
Fax: +86 21 5237 6549  
Email: info-china@piab.com

### INDIA

Piab Vacuum Technology Pvt. Ltd  
Plot no 11/C8 ,11 th block,  
Mugappair East,  
IN-600 037 CHENNAI  
Phone: +91 9444 25 36 48  
Email: info-india@piab.com

## JAPAN

Piab Japan Ltd.  
3-11-23 Hikawacho,  
JP-335-0027 TODA-SHI  
Phone: +81 48 443 9148  
Fax: +81 48 443 9179  
Email: info-japan@piab.com

## SINGAPORE

Regional office Asia Pacific  
Piab Asia Pte Ltd  
4008 Ang Mo Kio Ave 10  
03-16 Techplace 1  
SG-569625 SINGAPORE  
Phone: +65 6455 7006  
Fax: +65 6455 0081  
Email: info-singapore@piab.com

## SOUTH KOREA

Piab Korea Ltd  
C-1906 Daelim Acrotel  
KR-Kangnam-Gu 467-6  
DOKOK-DONG  
Phone: +82 2 3463 0751  
Fax: +82 2 3463 0754  
Email: info-korea@piab.com

## EUROPE

### FRANCE

Piab  
Parc d'entreprises L'Esplanade  
10 rue Enrico Fermi  
Saint-Thibault des Vignes  
FR-77462 LAGNY SUR MARNE Cedex  
Phone: +33 1 6430 8267  
Fax: +33 1 6430 8285  
Email: info-france@piab.com

### GERMANY

Regional office Europe  
Piab Vakuum GmbH  
Schorbachstr. 9  
DE-35510 BUTZBACH  
Phone: +49 6033 80600  
Fax: +49 6033 80699  
Email: info-germany@piab.com

## GREAT BRITAIN

Piab Ltd.  
Vacuum Innovation House  
Station Road  
GB-LE12 6LQ EAST LEAKE  
Phone: +44 1509 857 010  
Fax: +44 1509 857 011  
Email: info-uk@piab.com

## ITALY

Piab ITALIA Srl  
Via Cuniberti, 58  
IT-10151 TORINO  
Phone: +39 011 226 36 66  
Fax: +39 011 226 21 11  
Email: info-italy@piab.com

## POLAND

Piab Polska Sp. z o.o.  
Ul. Astronomow 1  
PL-80-299 GDANSK  
Phone: +48 58 785 08 50  
Fax: +48 58 785 08 51  
Email: info-poland@piab.com

## SPAIN

Vacío Piab, S.L.  
Avda. Pineda, 2  
CASTELLDEFELS  
ES-08860 BARCELONA  
Phone: +34 93 6333876  
Fax: +34 93 6380848  
Email: info-spain@piab.com

## SWEDEN

Head office  
Piab AB  
Box 4501  
SE-183 04 TÄBY  
Phone: +46 8 630 25 00  
Fax: +46 8 630 26 90  
Email: info-sweden@piab.com

## SWITZERLAND

Piab Vakuum AG  
Stückirain 1  
CH-3266 WILER BEI SEEDORF  
Phone: +41 32 391 21 10  
Fax: +41 32 391 21 11  
Email: info-ch@piab.com

**No need to compromise.**

[www.piab.com](http://www.piab.com)